




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
814	A	Released	JWM	4/22/03	HO	4/22/03	DJC	4/22/03
1498	B	Spec updated	JWM	2/11/04	JC	2/12/04	JC	2/12/04



NOTES:

- Material: Tefzel®
- Color: Blue
- Max. Bundle Dia.: 1.750 [44.45]
- Min. Bundle Dia.: .063 [1.59]
- Min. Loop Tensile Strength: 30 lbs
- Operating Temp: -50°F to 302°F [-46°C~150°C]
- Flame Rating: UL94V-0
- Gamma Radiation Resistance: 2×10^8 Rads
- Specifications: UL2043, ASTM D-3159 Type1 Grade 1

Tefzel® is a registered trademark of E.I. DuPont Corp.

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

Jeff McVicker

DATE:

4/22/03

CHECKED BY:

Hisham Odish

DATE:

4/22/03

APPROVED BY:

Daniel Carey

DATE:

4/22/03

DRAWING TITLE:

Cable Tie, Tefzel, Blue, 30 Pound Tensile

SIZE

A

DWG. NO.

8409-0361

ELECTRONIC FILE

16N851.dwg

REV

B

SCALE: NTS

U.O.M.: INCHES [mm]

SHEET: 1 OF 1