

7

6

5

4

3

2

1

SRK - BS - FL - ST - 001

SERIES PREFIX

BACKSHELL

BS

SIZE

FL

FULL

VERSION OF CORRUGATED CONDUIT
001 NW22
002 NW26

ST STRAIGHT

REV
B

SRK-BS-FL-ST-***

REVISIONS

SYM	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE PER E.O. P20387	12-1-09	R.D.R.
B	REVISED AND REDRAWN PER E.O. P20600	8/31/10	RDR

CONVOLUTE REQUIREMENTS:

RATED 125°C

NW22

OUTER Ø=25.40 [1.000]

INNER Ø=21.30 [.839]


PITCH=3.10 [.122]

NW26




OUTER Ø=31.20 [1.228]

INNER Ø=25.80 [1.016]

PITCH=3.40 [.134]



VERSION OF CONDUIT	X mm [inches]	Y mm [inches]	Z mm [inches]
001	33.00 [1.299]	21.50 [.846]	3.10 [.122]
002	32.00 [1.260]	26.40 [1.039]	3.50 [.138]

**SECTION A-A**

4. MATERIAL: PLASTIC; COLOR: BLACK.

3. THIS PART SNAPS ONTO SRK02-FL-*** AND SRK06-FL-***
* = KEYS; *** = SEE 37322C-00013-01 FOR ARRANGEMENTS.

2. DIMENSIONAL TOLERANCE: ±.64 [.025].

1. ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].

NOTES: UNLESS OTHERWISE SPECIFIED

SIGNATURE & DATE	
DR	JAIME APOSTOL 30AUG2010
CHK	D.M. 8/31/10
PE	D.M. 8/31/10
APPD	R. 8/31/10
SCALE	NONE
WT	32.20 g

BACKSHELL STRAIGHT
FULL SIZE (FL)
SRK SERIES

ENVELOPE

EP 201

MAIL CODE 89

3850 INDUSTRIAL AVE.
HEMET, CA 92545DEUTSCH
INDUSTRIAL

C

SRK-BS-FL-ST-***

DWG

CODE 11139

SHEET 1 OF 1

7

6

5

4

3

2

1