


REV.	DATE	DESCRIPTION
A	05/01/04	UPDATE DRAWING FORMAT



NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN () ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex						
8						DRAWN	G.R.S.					05/01/04		
7						CHECKED								
6	HEAT SHRINK TUBING		BLACK	1					PART DESCRIPTION					
5	FERRULE	COPPER	GOLD	1					SMA R/A CRIMP PLUG (FOR RG-178B/U, 196A/U)					
4	COVER	BRASS	GOLD	1					PART NO.					
3	CONTACT PIN	BRASS	GOLD	1					132173					
2	INSULATOR	TEFLON	NATURAL	1				DWG. NO.						
1	HOUSING/BODY	BRASS	GOLD	1				132173.DWG						
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE	C:/132/132173.DWG	REV.	A	SIZE	A	SCALE	NA