

CONTACT BeCu
PLATED GOLD

PART NO: 73366-0060/73366-0062/73366-0063/73366-0064






BODY BRASS
PLATED NICKEL

PART NO: 73366-0061/73366-0065/73366-0066

BODY BRASS
PLATED GOLD

PART NO 73366-0062/73366-0064/7336-0066
PACKAGING WITH TAPE & REEL
SEE SHEETS 2 & 3 FOR PACKAGING
INSTRUCTIONS

SEE SD-73366-619 FOR CONTINUATION OF TABULATION




$$\phi \frac{4.50}{177} \text{ REF}$$


SUGGESTED PCB LAYOUT

73366-0069	.280±.006	7.10±0.15	.062±.006	1.57±0.15	.073±.006	1.86±0.15	1 PC 73366-0061 PER BAG
73366-0068	.280±.006	7.10±0.15	.062±.006	1.57±0.15	.073±.006	1.86±0.15	73366-0060,SMALL TRAY
73366-0067	.280±.006	7.10±0.15	.062±.006	1.57±0.15	.073±.006	1.86±0.15	1 PC 73366-0060 PER BAG
73366-0066	.236±.006	5.99±0.15	.019±.006	0.5±0.15	.031±.006	0.8±0.15	TAPE & REEL
73366-0065	.236±.006	5.99±0.15	.019±.006	0.5±0.15	.031±.006	0.8±0.15	BY BAG
73366-0064	.236±.006	5.99±0.15	.019±.006	0.5±0.15	.031±.006	0.8±0.15	TAPE & REEL
73366-0063	.236±.006	5.99±0.15	.019±.006	0.5±0.15	.031±.006	0.8±0.15	BY BAG
73366-0062	.280±.006	7.10±0.15	.062±.006	1.57±0.15	.073±.006	1.86±0.15	TAPE & REEL
73366-0061	.280±.006	7.10±0.15	.062±.006	1.57±0.15	.073±.006	1.86±0.15	BY BAG
73366-0060	.280±.006	7.10±0.15	.062±.006	1.57±0.15	.073±.006	1.86±0.15	BY BAG

	IN	MM	IN	MM	IN	MM	PACKAGE	PS-73598-0132	ELECTRO/MECH. PERFORM.				
PART NO.	A		B		C			SPECIFICATION	DESCRIPTION				
CHG: ADD -0069 EC NO: URF2011-0644 DRWN: WIENER CHKD:SSS APPR: WIENER 2011/05/02 2011/05/02 2011/05/03 DESCRIPTION REV B9								QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
								▽=0		MM/IN			
								▽=0		mm INCH	DRAWN BY DATE	TITLE	
									4 PLACES ± --- ± ---	LYNN 2001/04/03	MCX JACK VERT PCB TH		
									3 PLACES ± --- ± ---	CHECKED BY DATE	50 OHMS		
									2 PLACES ± --- ± ---	JOHNSON 2001/04/03	MCX-J/PCB EWR-3263		
									1 PLACE ± --- ± ---	APPROVED BY DATE			
									ANGULAR ± 2 °	MISEN 2001/04/03	 MOLEX INCORPORATED		
									DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	MATERIAL NO.	DOCUMENT NO.	SHEET NO.	
										SEE TABLE	SD-73366-006	1 OF 3	
		SIZE ()	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										

NOTE:
1. 10 PITCHES CUMULATIVE TOLERANCE ±0.20(.008)



SECTION Z-Z

CHG: SEE SHEET 1
EC NO: URF2011-0644
DRWN: WIENER
CHKD: SSS
APPR: WIENER

QUALITY SYMBOLS
=0
=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± ---	± ---
1 PLACE	± ---	± ---

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY
LYNN

DATE
2001/04/03

CHECKED BY
JOHNSON

DATE
2001/04/03

APPROVED BY
MISEN

DATE
2001/04/03

MATERIAL NO.
SEE SHEET 1

SIZE
C

SCALE
DESIGN UNITS
METRIC

THIRD ANGLE PROJECTION


TITLE
MCX JACK VERT PCB TH
50 OHMS
MCX-J/PCB EWR-3263

MOLEX INCORPORATED


DOCUMENT NO.
SD-73366-006

SHEET NO.
2 OF 3

24.43
.962 MIN



LABEL:
- ORDER NO.
- QUANTITY
- PART NUMBER
- LOT NO.



NOTES:

- 1.MATERIAL :PS BLACK-THICKNESS:0.40±0.05mm
- 2.PACKING LENGTHH PER: 22" REEL: 35 METERS
- 3.COMPONENT LOAD PER: 13" REEL: 900PCS

CHG: SEE SHEET 1

EC NO: URF2011-0644
DRWN:JWIENER 2011/05/02
CHKD:SSS 2011/05/02
APPR:JWIENER 2011/05/03

REV DESCRIPTION

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± ---
2 PLACES	± ---	± ---
1 PLACE	± ---	± ---

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE	
MM/IN	
DRAWN BY	DATE
LYNN	2001/04/03
CHECKED BY	DATE
JOHNSON	2001/04/03
APPROVED BY	DATE
MISEN	2001/04/03

MATERIAL NO.
SEE SHEET 1

SIZE
C

SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
	METRIC	
TITLE		
MCX JACK VERT PCB TH		
50 OHMS		
MCX-J/PCB EWR-3263		
MOLEX INCORPORATED		
DOCUMENT NO.		SHEET NO.
SD-73366-006		3 OF 3

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION