




CATALOG LISTING
2PB970-T2
PAGE 1 OF 1
RELEASE NO. 200738
CHECK
REVISIONS
A CO18499
SV
23FEB06
CHECK
28 JUN 00
S A V
CHECK
28 JUN 00
DLT
FORMTEK
DRAWN



PANEL DETAIL


NOTES

- 1 - UNIT INCLUDES 2X "11SM" TYPE BASIC SWITCH SEALED IN COVER
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- ⚠ - MOUNTING HARDWARE FURNISHED UNASSEMBLED.

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE ----- 35 OZ APPROX	CONTACT ARRANGEMENT 2X S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
TOTAL TRAVEL ----- .105 APPROX	250 VAC ----- 5 AMP		
	30 VOLTS DC RATING	ONE PLACE (.0) ± .030	± .030
	INDUCTIVE RESISTIVE	TWO PLACE (.00) ± .015	± .015
	SEA LEVEL 50,000 FT 3 AMP 2.5 AMP 5 AMP 5 AMP	THREE PLACE (.000) ± .005	± .005
	MAXIMUM INRUSH ----- 24 AMP	ANGLES	±
		WEIGHT	