






COUPLER, RJ-45
CATEGORY: SEE TABLE, 8 POSITION
HOUSING: THERMOPLASTIC
CONTACTS: PHOSPHOR BRONZE, GOLD OVER NICKEL





PANEL GASKET
ELASTOMER, COLOR: ORANGE



RECEPTACLE HOUSING
POLYESTER, COLOR: BLACK



SUGGESTED PANEL CUTOUT



- 1. CONNECTOR MAY BE FRONT OR REAR MOUNTED TO A MAXIMUM PANEL THICKNESS OF 3.2 mm.
- 2. COUPLER LINES CROSSOVER BETWEEN PORTS.
- 3. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.
- 4. PANEL NUT AND PANEL GASKET ARE PACKAGED UNASSEMBLED IN POLYBAG.
- 5. COUPLER BONDED TO HOUSING BY ADHESIVE ALONG EDGE WHERE COUPLER MEETS HOUSING, SEE TABLE.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.L. KOLLER 25MAR04	TE Connectivity			
		CHK J. LANDIS 26MAR04				
		APVD S. HEADER 17JUN	NAME			
DIMENSIONS:		PRODUCT SPEC	RECEPTACLE KIT, INDUSTRIAL CIRCULAR ETHERNET CONNECTOR			
mm		108-2198				
		APPLICATION SPEC				
		114-13136				
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		-	A2	00779	1738601	-
			SCALE	5:2	SHEET	OF
					1	1
					REV	CI