



TABLE

ITEM NO	L
1065	2000mm±20MM
1066	3000mm±30MM

1.CABLE:NO UL,2BAWG(7/0.127),TINNED AND STRANDED COPPER WIRE  
 INSULATOR:PVC,ID:0.85mm ,CABLING:7C+DRAIN WIRE  
 SHIELD:AL/MY COVERAGE  
 JACKET:PVC,COMPLIANCE ROHS,COLOR:BEIGE,D.D:5mm

2.1PCS CONNECTOR:DB-SUB 25 WAYS MALE SOLDER TYPE CONNECTOR  
 INSULATOR:P.B.T.+GLASS FIBER,COLOR:BLUE  
 CONTACT:COPPER ALLOY,GOLD FLASH OVER NICKEL PLATED  
 SHELL:NICKEL PLATED.  
 CONNECTOR COMPLIANCE ROHS

3.1PCS CONNECTOR:DB-SUB 25 WAYS FEMALE SOLDER TYPE CONNECTOR  
 INSULATOR:P.B.T.+GLASS FIBER,COLOR:BLUE  
 CONTACT:COPPER ALLOY,GOLD FLASH OVER NICKEL PLATED  
 SHELL:NICKEL PLATED.  
 CONNECTOR COMPLIANCE ROHS

4.HOOD:PVC MOLDED TYPE WITH FOIL SHIELDED ON INNER  
 ON INNER MOLD AND INJECTION OUTER MOLD WITH  
 THUMB SCREW#4-4B UNC  
 COLOR:BEIGE,COMPLIANCE ROHS

5.Fulfill ROHS Guideline  
 6.ELECTRONIC TEST: 100% OPEN SHORT+MISS WIRE TEST

PIN OUT

DB25PIN PLUG(P1)	WIRE	DB25PIN FEMALE(J1)
2	---	3
3	---	2
4	---	5
5	---	4
6+8	---	20
20	---	6+8
7	---	7
SHELL	DRAIN WIRE	SHELL

PART NO	SHEET NO	1	THIRD ANGLE PROJECTION
TITLE: DB25 PIN MALE TO DB25 PIN FEMALE BEIGE COLOR		SCALE	N.T.S
		SIZE	A4
DWN NO		UNIT	mm INCH
		<input checked="" type="checkbox"/> mm	<input type="checkbox"/> INCH
		DRAWN BY & DATE	
		CHECKED BY & DATE	
		APPROVED BY & DATE	