





LOC	DIST	REVISIONS					
FT	8	P	LTR	DESCRIPTION	DATE	DWN	APVD
			V	REDRAWN W/O CHANGE PER EC 0020-1300-96	06 DEC 95	-	-
			W	REV PER EC 0320-82-97	13 AUG 97	BC	GS



- | | | | |
|---|---|-------------|---|
| ① | PHENOLIC PER MIL-M-14, TYPE CFG, BLACK. | 0.28±0.03 | → |
| ② | DIALLYL PHTHALATE PER MIL-M-14, TYPE SDG-F, BLUE. | [.011±.001] | |
3. WHEN MATING WITH BLOCK 201356, ACCOMODATES TYPE II, TYPE III+ OR TYPE VI #16 PIN OR SOCKET CONTACTS.

	200346-4
	200346-2
MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 06 DEC 95 C. REIFSNYDER		AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		AMP	
		0 PLC ±— 1 PLC ±— 2 PLC ±0.13 [.005] 3 PLC ±— 4 PLC ±— ANGLES ±—		NAME BLOCK, FEMALE, 20 PLACE MINIATURE RECTANGULAR, M SERIES	
MATERIAL SEE TABLE		FINISH —		SIZE A2 CAGE CODE 00779 DRAWING NO C=200346	
		WEIGHT —		SCALE 4.1 SHEET 1 OF 1 REV W	
		CUSTOMER DRAWING			