




パネル取付穴寸法 (板厚 1.52 最大)
MOUNTING IN () ARE REFERENCES
1.52 THK MAX

注記
NOTE

1. ELV 及び RoHS 適合品
ELV AND RoHS COMPLIANT

無 WITHOUT	39-01-7039	I625-03R1-RE
無 WITHOUT	39-03-2035	I625-03R1
有 WITH	39-03-2034	I625-03R
MTG.EARS	EDP.NO	ENG.NO

REVISED EC NO: J2007-2743 DRWN: YAMADA01 CHKD: THARUYAMA APPR: NUKITA		DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			10 UNDER	±0.2	DRAWN BY Y. ASHIZAWA	DATE 1988/03/10	TITLE .062 DIA. RECEPTACLE HOUSING				
			10 OVER 30 UNDER	±0.25	CHECKED BY H. HIRAMOTO	DATE 1995/09/05					
			30 OVER	±0.3	APPROVED BY M. FUKUSHIMA	DATE 1995/09/05	MOLEX INCORPORATED				
			ANGULAR	±3 °	MATERIAL NO.		DOCUMENT NO.				SHEET NO.
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-1625-001				1 OF 1
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
MATERIAL ナイロン66 UL94V-2		REV									

MATERIAL
+10x66
UL94V-2