



MATERIAL
HOUSING : G.F. 15% PBTP (UL94V-0)
TERMINAL : PHOSPHOR BRONZE

2. 適用電線： 1.27 ピッチリボンケーブル 被覆外径： Ø 1.14 MAX.
 より線： AWG#26 ~ #28 (芯線 7 本構成)
 単線： AWG#28

FOR USE WITH AWG#26 & #28 STRANDED WIRE (CONSISTS OF 7 CONDUCTORS)
AND #28 SOLID WIRE.
1.14(.045) DIA. MAX. INSULATION RIBBON CABLE WITH 1.27(.050) CENTERS.

3. 適合ストレインリリーフ: 5328-N
MATES WITH STRAIN RELIEF OF 5328 SERIES.
4. 嵌合相手: 5330,5332,5340,5342,5576,5578 シリーズ
MATES WITH CONNECTOR SERIES OF 5330,5332,5340,5342,5576 & 5578.

5. 使用符号の説明 LEGEND 5320 - N B * - *

ベースナンバー
BASE NUMBER


極数
CIRCUIT SIZE

アッパハウジング組付タイプ
PRELOADED UPPER HOUSING

ターミナルのメッキコード
PLATING CODE OF TERMINAL

MATERIAL COLOR
BLANK : BLACK
GY : GREY

64	78.74	82.54	85.91
60	73.66	77.46	80.83
50	60.96	64.76	68.13
44	53.34	57.14	60.51
40	48.26	52.06	55.43
34	40.64	44.44	47.81
30	35.56	39.36	42.73
26	30.48	34.28	37.65
20	22.86	26.66	30.03
16	17.78	21.58	24.95
14	15.24	19.04	22.41
12	12.70	16.50	19.87
10	10.16	13.96	17.33
極大 No. OF CKTS.	A 寸法 DIM. A	B 寸法 DIM. B	C 寸法 DIM. C



REVISED	EC NO: J2006-0433 DRAWN: A YANAGI MOTO 2005/08/09 CHKD: M TANAKA 2005/08/17 APPR: NUKI I TA 2005/08/24	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
			10 UNDER	± 0.2	DRAWN BY H. HIRAMOTO	DATE 1990/07/11	TITLE QIK FLECS FEMALE ASS'Y			
			10 OVER 30 UNDER	± 0.25	CHECKED BY					DATE
			30 OVER	± 0.3	APPROVED BY		DATE	 MOLEX INCORPORATED		
			ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.			
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE SHEET 2		SD-5320-003		1 OF 2	
REV	J		SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

