








SECTION X-X'
SCALE 10:1

ISOMETRIC



NOTES

- MATING WAFER : 35337-10, -20
- MATERIAL 1) HOUSING : PBT UL94V-0 (GLASS 15%)
2) TERMINAL : PHOS-BRO, PRE-TINNED
- CAMBER 0.2 MAX.
- KINK TABLE (N : CKTS)

	CKT	1	2	3	4	5	N-2	N-1	N
6 CKT OVER	-	a	b	-	-	b	a	-	-
5 CKT	a	b	-	b	a	-	-	-	-
4 CKT	a	b	b	a	-	-	-	-	-
3 CKT	a	b	a	-	-	-	-	-	-

5. GENERAL TOLERANCES

GENERAL TOLERANCES		
10 UNDER		± 0.2
10 OVER 30 UNDER		± 0.25
30 OVER		± 0.3
ANGLE		± 3°

38.5	35	35238-1510	15	18.5	15			26	22.5	35238-1010	10
36	32.5	-1410	14	16	12.5			23.5	20	-0910	9
33.5	30	-1310	13	13.5	10			21	17.5	-0810	8
31	27.5	-1210	12	11	7.5					-0710	7
28.5	25	35238-1110	11	8.5	5					-0610	6
B	A	ENG. NO.	CKT	B	A	ENG. NO.	CKT			-0510	5
										-0410	4
										35238-0310	3

				MATERIAL PBT, UL94V-0 VALOX DR-48(NATURAL)		 MOLEX-KOREA CO.,LTD.	
				GENERAL TOLERANCE DIMENSION : ±0.1 ANGLE : ± 1°		DRAWN BY K.S.KIM	
				DIMENSION CLASSIFICATION ▽ : CRITICAL ▼ : MAJOR () : REFERENCE		CHK'D BY	
B	REVISED	96-092	960809			APP'D BY	
A	NEW RELEASED	96-064	960711			SCALE 8:1	
LTR	REVISION RECORD	ECN	DATE	ASS'Y PART DESCRIPTION ENG. NO.		TITLE; 2.5 PITCH B/B CONN. HOUSING ASS'Y(R/A)	
REVISE ONLY ON CAD SYSTEM				RECEPACLE TERMINAL 35071-8001		ENG. NO. SD 35238-..10	
						REV B	