







注記
NOTES:

- 材質：銅合金
MATERIAL : COPPER ALLOY
- メッキ仕様
PLATING
錫メッキ：3μm 以上
TIN PLATING : 3 MICROMETER MIN.
ニッケルメッキ：1μm 以上 (下地メッキ)
NICKEL PLATING : 1 MICROMETER MIN. (UNDER PLATING)
- 適用電線及び適合ハウジング
APPLICABLE WIRE AND APPLICABLE HOUSING

適合ハウジング APPLICABLE HOUSING	51240-**** (5mm PITCH)	51241-**** (7.5mm PITCH)
適用電線 APPLICABLE WIRE		
範囲 RANGE	AWG#16 ~ #18	AWG#14 ~ #18
被覆外径 (UL1015相当) INS. DIA. (UL1015 CORRESPONDING)	ø3.4 MAX.	ø3.8 MAX.

- 本製品は 56125-0018 / 0118 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 56125-0018 / 0118.

連鎖状 CHAIN	56125-0028
バラ状 LOOSE	56125-0128
端子形状 FORM	製品番号 MATERIAL NO.

RELEASED EC NO: J2005-2082 DRAWN: AIDA CHKD: KTOJO APPR: NUKITA 2005/01/20 2005/01/24 2005/01/28	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
		10 UNDER	±0.2	DRAWN BY N. AIDA	DATE '05/01/20	TITLE MTC(MULTI TERMINAL CONN) REC. CRIMP TERM. -LEAD FREE-		
		10 OVER 30 UNDER	±0.25	CHECKED BY K. TOJO	DATE '05/01/20			
		30 OVER	±0.3	APPROVED BY N. UKITA	DATE '05/01/20			
		ANGULAR ±3 °		MATERIAL NO.			DOCUMENT NO.	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-56125-004		1 OF 1	
	REV 0	SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						