



1 2 3 4 5 6

A


B

C

D



Abisolierlänge: 13mm
 stripping length: 13mm
 Anzugsmoment: 10mm² 16mm² 25mm²
 Tightning torque: 6Nm 6Nm 7Nm
 für Litze 10-25mm², AWG 6-4, feindrähtig
 for stranded wire 10-25mm², AWG 6-4, fine wire



ALL Dimensions in mm Original Size DIN A 4		Techn. Character.			Nicht tolerierte Maße/Free size tolerances	
			Dat.	Name	Maßstab/Scale 2:1	100A Axialschraubkontakt Buchse 100A axial screw contact, female 10-25mm ² versilbert/silver plated
		Detail.	15.07.11	gru		
		Insp.		Rü		
		Stand.				
A		HARTING Electric GmbH & Co. KG				TB 09 11 000 6212
Mod.	Dat.	Name	D-32339 Espelkamp			
					Sub.	