




Abisolierlänge: 13mm
stripping length: 13mm
 Anzugsmoment: 10mm² 16mm² 25mm²
Tightning torque: 6Nm 6Nm 7Nm
 für Litze 10-25mm², AWG 6-4, feindrähtig
for stranded wire 10-25mm², AWG 6-4, fine wire



			All Dimensions in mm Original Size DIN A 4				Techn. Character.			Nicht tolerierte Maße/Free size tolerances			
				Dat.	Name	Maßstab/Scale 2:1	100A Axialschraubkontakt, Stift 100A axial screw contact, male 10-25mm ² versilbert/silver plated			TB 09 11 000 6112 Sub.		Blatt/ page /	
			Detail.	21.02.11	gru								
			Insp.		Rü								
			Stand.										
						HARTING Electric GmbH & Co. KG							
A						D-32339 Espelkamp							
Mod.	Dat.	Name											