


Abisolierlänge: 13mm
 stripping length: 13mm
 Anzugsmoment: 16mm² 25mm² 35mm²
 Tightning torque: 6Nm 7Nm 8Nm
 für Litze 16-35mm², AWG 4-2, feindrähtig
 for stranded wire 16-35mm², AWG 4-2, fine wire



All Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Maß/Free size tolerances			
				Dat.	Name	Maßstab/Scale 2:1	100A Axialschraubkontakt, Buchse 100A axial screw contact, female 16-35mm ² versilbert/silver plated		
			Detail.	15.07.11	gru				
			Insp.		Rü				
			Stand.						
A			HARTING Electric GmbH & Co. KG D-32339 Espelkamp				TB 09 11 000 6213		
Mod.	Dat.	Name							