




F




E




D



C




B




A

アクチュエータ開放位置
ACTUATOR OPENING POSITION




偶数端子



SECTION Y-Y

奇数端子




SECTION X-X

注記 NOTES

1. 使用材料 MATERIALS
ハウジング : 液晶ポリマー(ガラス充填, UL94V-0, ページュ)
アクチュエータ : ポリアミド(ガラス充填, UL94HB, 黒色)
奇数端子 : 銅合金
偶数端子 : 銅合金
補強金具 : 銅合金
HOUSING : LIQUID CRYSTAL POLYMER (GLASS FILLED, BEIGE)
ACTUATOR : POLYAMIDE (GLASS FILLED, BLACK)
ODD TERMINAL : COPPER ALLOY
EVEN TERMINAL : COPPER ALLOY
FITTING NAIL : COPPER ALLOY
2. メッキ仕様 PLATING
端子 TERMINAL
テール部 : 部分金メッキ
接点部 : 部分金メッキ 0.1μm MIN.
下地 : ニッケルメッキ 1.0μm MIN.
TAIL AREA : SEPARATED GOLD PLATING
CONTACT AREA : SEPARATED GOLD PLATING 0.1μm MIN.
UNDER PLATING : NICKEL PLATING 1.0μm MIN.
- 金具 FITTING NAIL
テール部 : スズメッキ 0.5μm MIN.
下地 : ニッケルメッキ 1.0μm MIN.
TAIL AREA : TIN PLATING 0.5μm MIN.
UNDER PLATING : NICKEL PLATING 1.0μm MIN.
3. 端子、補強金具のコプラナリティーは 0.1 以下とする
COPLANARITY OF SOLDER TAILS AND FITTING NAILS : 0.1MAX.
4. 一般公差 : ±0.3
GENERAL TOLERANCES: ±0.3
5. ELV & RoHS COMPLIANT.

11.34	10.5	9.5	10.0	12.0	503320-4160	41
10.34	9.5	8.5	9.0	11.0	503320-3760	37
7.34	6.5	5.5	6.0	8.0	503320-2560	25
E	D	C	B	A	EMBOSSED PACKAGE オーダー番号 ORDER NO.	極数 CIRCUITS
CONNECTOR SERIES NO. 503320-***68						

REVISED EC NO: J2012-0779 DRAWN: TANAKA CHKD: SHOH KAWA APPR: SHOH KAWA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 20:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± ---	M. TAKASAKI	2009/05/20	0.25 PITCH FPC CONN E/O HGT=1.65 BTM CONTACT				
		10 OVER 30 UNDER	± ---	CHECKED BY M. HAYASHI	2009/05/20					
		30 OVER	± ---	APPROVED BY N. UKITA	2009/05/20	MOLEX INCORPORATED				
		ANGULAR ±1 °		MATERIAL NO.						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-503320-001		1 OF 2		
	REV			SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				





注記 NOTES


- 製品詳細寸法については図面 SD-503320-001 を参照下さい。
RE DETAILED DIMENSION, SEE SD-503320-001
- 梱包数量 : 3000 個/リール
NUMBER OF CONNECTORS : 3000 PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH

引き出し方向
PULL OUT
DIRECTION


REEL



DETAIL "C"




引き出し方向
PULL OUT
DIRECTION



- 材料 MATERIAL
キャリアテープ (CARRIER TAPE) : ポリスチレン (POLYSTYRENE)
トップテープ (TOP TAPE) : PET , PE , PEF
リール (REEL) : ポリスチレン (PS) <リサイクル材を含む>
POLYSTYRENE (PS) <RECYCLE MATERIAL CONTAINED>
- ELV & RoHS COMPLIANT

RELEASED EC NO.: J2010-0413 DRWN: CARIZONO 2009/09/15 CH'KD: T. HARUYAMA 2009/09/15 APPR: NUKITA 2009/09/15 REV: 0	DESCRIPTION GENERAL TOLERANCES (UNLESS SPECIFIED) 10 UNDER ± --- 10 OVER 30 UNDER ± --- 30 OVER ± --- ANGULAR ± --- ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE MM ONLY DRAWN BY: C. ARIZONO CHECKED BY: T. HARUYAMA APPROVED BY: N. UKITA DATE: 2009/05/20 DATE: 2009/05/20 DATE: 2009/05/20	SCALE --- TITLE 0.25MM PITCH FPC CONN HGT=1.65 HSG ASSY EMBOSSED TAPE PACKAGE MOLEX INCORPORATED SEE CHART	MATERIAL NO. 503320-**60 DESIGN UNITS METRIC THIRD ANGLE PROJECTION	SHEET NO. 1 OF 2



24	11.5	29.4	25.4	12.3	503320-4160	41
				11.3	503320-3760	37
				8.3	503320-2560	25
E キャリアテープ幅 CARRIER TAPE WIDTH	(D)	C	B	(A)	EMBOSSED PACKAGE	極数
					オーダー番号 ORDER NO.	CKT.
MATERIAL NO. 503320-**60						

RELEASED EC NO: J2010-0413 DRWN: CARIZONO 2009/09/15 CHKD: T. HARUYAMA 2009/09/15 APPR: NUKITA 2009/09/15 REV: 0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± ---	DRAWN BY C. ARIZONO	DATE 2009/05/20	TITLE 0.25MM PITCH FPC CONN HGT=1.65 HSG ASSY EMBOSSED TAPE PACKAGE MOLEX INCORPORATED				
		10 OVER 30 UNDER	± ---	CHECKED BY T. HARUYAMA	DATE 2009/05/20					
		30 OVER	± ---	APPROVED BY N. UKITA	DATE 2009/05/20					
		ANGULAR	± --- °	MATERIAL NO.						
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-503320-002		2 OF 2			
	REV			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						