






REV
NC DTMH04-2P*

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. PI9769	3-17-09	ADR



- 8 SEE SHEET 2 FOR OTHER KEY ARRANGEMENTS.
7. RECEPTACLE IS RATED AT 150°C.
6. MATERIAL - HOUSING: PLASTIC; GROMMET/SEAL: RUBBER
5. THIS RECEPTACLE MATES WITH DTMH06-2S* AND DTM06-2S* PLUG.
(* = A,B,C,D KEYS).
- 4 FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.
- 3 TERMINAL POSITION ASSURANCE (TPA) LOCK PRE-MOUNTED: WMH-2S*
(* = A,B,C,D KEYS)
2. ALL DIMENSIONS ARE ±.025 [0.64].
1. ALL DIMENSIONS ARE IN INCHES [mm].

NOTES: UNLESS OTHERWISE SPECIFIED

CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIDE RANGE ⁴ [mm ²] REF ONLY
20	.053 [1.35]	.120 [3.05]	16-20 AWG [1.0-0.2]

SIGNATURE & DATE	
DR	D. MEYER 11-07-07
CHK	W. Whitaker 3/13/08
PE	D. Whitaker 3/12/08
APPD	D. Meyer 3/12/08
SCALE	NONE

RECEPTACLE
2 PIN CONT, SIZE 20
COLOR: BLACK
DTMH SERIES



ENVELOPE

EP 180	MATL. CODE
3850 INDUSTRIAL AVE. HEMET, CA 92545	
DEUTSCH INDUSTRIAL	
B	DTMH04-2P*
DWG SIZE	CODE 11139 SHEET 1 OF 2

REV
NC



DTMH04-2P*

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	SEE SHEET 1	3-17-08	ADR





DTMH04-2PA

-A- KEY
TPA COLOR: GREY





DTMH04-2PB

-B- KEY
TPA COLOR: BLACK



DTMH04-2PC

-C- KEY
TPA COLOR: GREEN



DTMH04-2PD

-D- KEY
TPA COLOR: BROWN

NOTES:

SIGNATURE & DATE	
DR	D. MEYER 11-07-07
CHK	<i>E. Brauch</i> 3/12/08
PE	<i>D. Whitacre</i> 3/12/08
APPD	<i>D. Meyer</i> 3/12/08
SCALE	NONE

RECEPTACLE
2 PIN CONT, SIZE 20
COLOR: BLACK
DTMH SERIES

ENVELOPE

EP 180	MATL. CODE
 3850 INDUSTRIAL AVE. HEMET, CA 92545	
B	DTMH04-2P*
DWG SIZE 11139	SHEET 2 OF 2