









REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. PI9884	6-16-08	ADR



8. SEE SHEET 2 FOR OTHER KEY ARRANGEMENTS.
7. PART MODIFICATION: RECEPTACLE IS RATE AT 150°C (COLOR: BLACK).
6. MATERIAL - HOUSING/RETAINER: PLASTIC; GROMMET: RUBBER.
5. CONNECTOR DESIGNED TO BE USED WITH DTM06-08S*-***** PLUGS.
(*) = A,B,C,D KEYS, (****) = ALL HIGH TEMPERATURE MODIFICATIONS.
CONSULT FACTORY FOR MODIFICATIONS.
4. FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.
3. SECONDARY WEDGE LOCK SOLD SEPARATELY: WM-8P.
2. DIMENSION TOLERANCE: $\pm .025$ [.64].
1. DIMENSIONS ARE IN INCHES [mm].
- NOTES: UNLESS OTHERWISE SPECIFIED

SIGNATURE & DATE	
DR	P. CARNAHAN 5/30/08
CHK	D. Meyer 6/16/08
PE	Paulo Carnahan 6/13/08
APPD	D. Meyer 6/16/08
SCALE	NONE


RECEPTACLE
8 CONTACTS, SIZE 20
A,B,C,D KEYS
-EE04 MOD
DTM SERIES

ENVELOPE


CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIRE RANGE [mm ²] REF ONLY
20	.053 [1.35]	.120 [3.05]	16-20 AWG [1.0-0.5]

EP 172	MATL. CODE
 3850 INDUSTRIAL AVE. HEMET, CA 92545	
B DTM04-08P*-EE04	
DWG SIZE	CODE 11139 SHEET 1 OF 2


REV NC	DTM04-08P*-EE04	REVISIONS			
		SYM	DESCRIPTION	DATE	APPROVED
		NC	SEE SHEET 1	6-16-08	RDR




DTM04-08PA-EE04
KEY -A-
COLOR: BLACK



DTM04-08PB-EE04
KEY -B-
COLOR: BLACK



DTM04-08PC-EE04
KEY -C-
COLOR: BLACK



DTM04-08PD-EE04
KEY -D-
COLOR: BLACK

NOTES:

SIGNATURE & DATE		RECEPTACLE 8 CONTACTS, SIZE 20 A,B,C,D KEYS -EE04 MOD DTM SERIES ENVELOPE	EP 172	MATL. CODE
DR	P. CARNAHAN 5/30/08		 3850 INDUSTRIAL AVE. HEMET, CA 92545	DTM04-08P*-EE04
CHK	<i>DMeyx</i> 6/16/08			
PE	<i>Paula Lano</i> 6/13/08			
APPD	<i>DMeyx</i> 6/16/08		B	CODE 11139
SCALE	NONE			
			DWG SIZE	SHEET 2 OF 2