






- 1 MATERIAL: CONNECTOR - NYLON UL94-V2
CONTACTS - 0.30[.012] THICK COPPER ALLOY
(BRIGHT TIN-LEAD 0.00203[.000080] MIN. THICK
FOR CONTACTS 641437-2 THRU 2-641437-4).
(MATTE TIN PLATE 0.00203[.000080] MIN. THICK
FOR CONTACTS 3-641437-2 THRU 5-641437-4).
- 2 CONTACTS ACCEPT #22 AWG SOLID, FUSED STRANDED OR
STRANDED (7 STRANDS) WIRE WITH 2.41 [.095] MAX INSULATION DIA.
- 3 BOW, IN ANY DIRECTION, NOT TO EXCEED 0.15 [.006] PER IN.
- 4 HOUSING FEATURES: CLOSED END.
- 5 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 7 RED COLOR STRIPE ON HOUSING (NOT SHOWN) MAY RUN DOWN BETWEEN RIBS.



SECTION A-A

6	OBSELETE SUPERSEDED	TIN	9.14	[.3588]	95.20	[3.748]	99.06	[3.900]	24	5-641437-4
			55.47	[2.184]	59.54	[2.344]	63.40	[2.496]	15	4-641437-5
			43.59	[1.716]	47.65	[1.876]	51.51	[2.028]	12	4-641437-2
			31.70	[1.248]	35.76	[1.408]	39.62	[1.560]	9	3-641437-9
			19.81	[.780]	23.88	[.940]	27.74	[1.092]	6	3-641437-6
			11.89	[.468]	15.95	[.628]	19.81	[.780]	4	3-641437-4
			7.92	[.312]	11.99	[.472]	15.85	[.624]	3	3-641437-3
			3.96	[.156]	8.03	[.316]	11.89	[.468]	2	3-641437-2
			91.14	[3.588]	95.20	[3.748]	99.06	[3.900]	24	2-641437-4
			55.47	[2.184]	59.54	[2.344]	63.40	[2.496]	15	1-641437-5
TIN-LEAD	43.59	[1.716]	47.65	[1.876]	51.51	[2.028]	12	1-641437-2		
	31.70	[1.248]	35.76	[1.408]	39.62	[1.560]	9	641437-9		
	19.81	[.780]	23.88	[.940]	27.74	[1.092]	6	641437-6		
	11.89	[.468]	15.95	[.628]	19.81	[.780]	4	641437-4		
	7.92	[.312]	11.99	[.472]	15.85	[.624]	3	641437-3		
	3.96	[.156]	8.03	[.316]	11.89	[.468]	2	641437-2		
	FINISH	C	B	A	NO. OF CIRCUITS	PART NUMBER				

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN S CARPENTER	23JUN05				
DIMENSIONS: mm [INCHES]				CHK D BOSSI	7/21/03	NAME	TE Connectivity		
				APVD D BOSSI	7/21/03				
				PRODUCT SPEC		MTA 156 POSTED CONNECTOR ASSEMBLY 22 AWG			
				—					
				APPLICATION SPEC					
				—					
MATERIAL —				WEIGHT —		SIZE A1	CAGE CODE 00779	DRAWING NO C-641437	RESTRICTED TO —
FINISH —				CUSTOMER DRAWING		SCALE 5:1	SHEET 1	OF 1	REV E