





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		P	REVISED PER ECR-11-018063	26DEC11	KH PD


- 1 CONTINUOUS STRIP ON REELS
- 2 ACCEPTS #18-#14 AWG WIRE SIZE
- 3 INSULATION RANGE IS .120-.170 DIA
- 4 MATING TAB THK IS .032±.001.
- 5 REELED WITH INTERLEAVING PAPER
- 6 PRELIMINARY - NOT FOR PRODUCTION



SECTION C-C



SECTION A-A



SECTION B-B

OBSOLETE	5 STANDARD	.000080 MIN TIN	6 1-63306-0
	REVERSE	-	63306-3
	STANDARD	TIN	63306-2
	STANDARD	-	63306-1
	REELING	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 20JUN02	TE Connectivity			
DIMENSIONS: INCHES		CHK P DESANTIS 20JUN02				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD P DESANTIS 20JUN02	NAME RECEPTACLE, FASTON, .250 SERIES			
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL 4M BRASS	FINISH SEE TABLE	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-63306	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 8:1	SHEET 1 of 1	REV P	