

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		C	ECR-09-002275	30MAR09	AM	JS

- NOTES:
- FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE.
 - ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED.
 - FOR PACKAGING DETAILS SEE SHEET 2.
 - UL NUMBER E13288
 - MATERIAL: BODY - COPPER
SLEEVE - PVC (K65), 94V-0
 - APPLICATION SPEC 114-13196

2-1838162-0	4.0mmsq-6.0mmsq 12-10 (AWG)	6mm STUD SIZE STANDARD ENTRY	YELLOW RING TERMINAL (INSULATED)	1000	500	6.40	12.00	32.70	6.70	14.00	1.00	0.80	4.0mmsq-6.0mmsq 12-10(AWG)	6.0	YELLOW RING TERMINAL (INSULATED)	2-1838162-0					
1-1838162-0				1750	50											1-1838162-0					
STOCK NUMBER	PACKING LABEL DESCRIPTION LINE 3	PACKING LABEL DESCRIPTION LINE 2	PACKING LABEL DESCRIPTION LINE 1	INNER CARTON QTY	QTY	d2 (±0.20)	B (±0.30)	L (±1.50)	D (±0.50)	E (±1.50)	t (±0.10)	t1 (±0.20)	WIRE SIZE (mmsq) & (AWG)	STUD SIZE (mm)	DESCRIPTION	PART No					
						DIMENSIONS															
										THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN K.Raghunandan 19JUL05		Tyco Electronics Corporation Bideford, UK, EX39 4HE						
										CHK S. Parlow 04/05/07		NAME									
										APVD F. Wheeler-King 04/05/07		PRODUCT SPEC			EURO-CRIMP INSULATED YELLOW RING TERMINAL 4.0mmsq-6.0mmsq / 12-10 AWG RANGE						
										APPLICATION SPEC		-									
										MATERIAL		FINISH			WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
										-		-			-		A2	00779	C=1838162	-	
CUSTOMER DRAWING													SCALE		NTS	SHEET	1	OF	2	REV	C

