








△	.146	RED/GREEN	RED/GREEN	1-5406552-9
	.100	RED/YELLOW	RED/GREEN	1-5406552-8
	.100	GREEN	-	1-5406552-7
	.126	RED/GREEN	RED/GREEN	1-5406552-6
	.100	SEE VIEW A (SHEET 2)	SEE VIEW A (SHEET 2)	1-5406552-5
	.100	RED	GREEN	1-5406552-4
	.100	GREEN/RED	GREEN/RED	1-5406552-3
	.120	YELLOW	GREEN	1-5406552-1
	.100	GREEN/ORANGE	YELLOW	5406552-9
	.100	GREEN/YELLOW	GREEN/YELLOW	5406552-8
△ OBSOLETE	.100	GREEN/ORANGE	GREEN/ORANGE	5406552-7
	.100	YELLOW	YELLOW	5406552-6
	.100	GREEN	GREEN	5406552-5
△ OBSOLETE	.100	GREEN	YELLOW	5406552-4
	.100	YELLOW	-	5406552-3
	.100	-	GREEN	5406552-2
	.100	YELLOW	GREEN	5406552-1
DIM A		POSITION 2	POSITION 1	PART NUMBER
SOLDERTAIL LENGTH		INDICATOR COLOR FOR EACH HOUSING		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DRN 10MAY2005 T. SPRINKLE/L.A.MAYER CHK 10MAY2005 J. WESTMAN APPROVED J. WESTMAN 10MAY2005		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLG ± 2 PLG ± 3 PLG ± 0.25[.01] 4 PLG ± 0.13[.005] 5 PLG ± ± 6 PLG ± ±		INVERTED MODULAR JACK ASSEMBLY, 1X4, SHIELDED, PANEL GROUND, WITH LED	
MATERIAL SEE NOTE 1		PART NUMBER 114-2154 WEIGHT —		SIZE A1 CAGE CODE 00779 DRAWING NO C5406552	
FINISH SEE NOTE 1		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 of 2 REV E	



VIEW A
(1-5406552-5 ONLY)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 104MAY2005 T. SPRINKLE/L.A.MAYER CHK 104MAY2005 J. WESTMAN S. FLICKINGER APD 104MAY2005		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± - 2. PLC ± 0.25 [0] 3. PLC ± 0.13 [0.05] 4. PLC ± - ANGLES ± -		NAME INVERTED MODULAR JACK ASSEMBLY, 1x4, SHIELDED, PANEL GROUND, WITH LED	
MATERIAL SEE NOTE 1		FINISH SEE NOTE 1		SIZE 108-1163-4 APPLICATION SPEC 114-2154	
WEIGHT -		SIZE A1		CAGE CODE 00779	
CUSTOMER DRAWING		DRAWING NO 5406552		RESTRICTED TO -	
		SCALE 4:1		SHEET 2 OF 2	
		REV F			