


P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	REVISED PER ECO-12-006586	16APR12	KH	DR



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
26-22 AWG STRANDED	NOT LISTED	NOT LISTED

- 1

STAMP AMP APPROX AS SHOWN
- 2

0.00254 [.000100] MIN TIN PER ASTM B-545
- 3

CLEANED, UNPLATED
- 4

0.00254 [.000100] MIN EXT THK GOLD PL PER
ASTM B-488 OVER 0.00076 [.000030] MIN NICKEL
PER QQ-N-290.
- 5

COPPER PER ASTM B-152, ANNEALED
- 6

NOTE DELETED

4	2-32859-5
3	32859-1
2	32859
FINISH	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 2-2-93	TE Connectivity			
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C		CHK DA PATTERSON 2-2-93				
FOR APPLICATION		TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: N/A		APVD JL MECKLEY 2-2-93	NAME			
TOOLING INFORMATION		1-800-526-5142	CIRCULAR MIL AREA: 0.1-0.41mm ² [202-810] STRANDED		PRODUCT SPEC —	TERMINAL, RING TONGUE, BUDGET —			
FOR ORDER ENTRY		1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C-32859	RESTRICTED TO —
					MATERIAL 5	WEIGHT —	CUSTOMER DRAWING		SCALE 10:1
							SHEET 1 OF 1	REV D2	