






NUMBER C-175271
METRIC
三角度 (3rd ANGLE PROJECTION)



- 注 ;
1. 取付適用規格番号 114-5159
 2. 適用製品規格番号 108-5374
- NOTE ;
1. APPLICATION SPEC NO. 114-5159
 2. APPLICABLE PRODUCT SPEC NO.108-5374

0.76µm以上	—#—	金めつき済 (SELECTIVE GOLD)	175271-3
—#—	179421-1	錫めつき済 (PRE-TINNIED)	175271-1
△金めつき厚 (GOLD PLATING THICKNESS)	バラ端子型番 (LOOSE PIECE CONTACT P/N)	仕上げ (FINISH)	AMP型番 (PART NUMBER)

E1	ADD NOTE 2	FJ00-0937-99	TS	KB	28MAY 99
E	改訂 (FJ00-0577-98)		TK	NS	25MAR 98
D	改訂 (FJ00-0182-94)		TS	KO	6/30 94
C	改訂 (FJ00-0153-94)		TK	MT	4/3 94
B	変更	J-12551	KO	SI	6/27 91
A	再作成		KO	SI	4/25 91
LTR	変更 (REVISION RECORD)		DR	CHK	DATE

Copyright ©1990 AMP (Japan), LTD. ALL RIGHTS RESERVED.

AMP 日本エー・エム・ピー株式会社 Tokyo, Japan

名称 (NAME) .040 II SERIES "S" TAB CONTACT
.040 IIシリーズ S タブ コンタクト

一般公差 (GENERAL TOLERANCE)
10以下: ±0.2
10を超え 30以下: ±0.25
30を超え 100以下: ±0.3
角 度: ±3°

尺度 (SCALE) 5-1

REV. E1

SHEET 1 OF 1

LOC B J

番号 (No.) C-175271

PRINT DIST
単位: 概 DIMENSIONS IN MM. DO NOT SCALE PRINT