




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-		B5	ECR-11-016022	03AUG2011	GW	BR
			C1	ECR-11-018403	07SEP2011	OH	BR
			C2	ECR-11-021475	24OCT2011	GW	BR




- Notes
- SUITABLE HOUSINGS: SERIES HC26
CUSTOMER DRAWING: 1103433, 1103434
 - OUTER DIMENSIONS OF INSULATION: MAX. Ø3.2 MM
 - SUITABLE CRIMP CONTACTS:
CUSTOMER DRAWING: 827040
 - SUITABLE SUB-MIN. COAXICON CONTACTS:
CUSTOMER DRAWING: 51563
 - SUITABLE LWL (OPTICS) CONTACTS:
CUSTOMER DRAWING: 216341
 - SUITABLE INSERTION TOOL:
CUSTOMER DRAWING: 1102855
 - SUITABLE EXTRACTION TOOL:
CUSTOMER DRAWING: 1102855
 - SUITABLE SIGNAL INSERT:
CUSTOMER DRAWING: 1103426
 - STANDARDS:
DIN EN 61984, DIN EN 60664-1
 - POLARIZATION RIPS
 - PACKAGING 0-1 /0-2:
40 SETS IN A CARTON
 - PACKAGING 0-3:
40 PIECE

PN 0-1 AS SHOWN

-	-	1	ADAPTOR RING	PA-66-GF25	GREY	SERIES HC26, INSERT	3
-	-	1	RETAINING RING	PA-66-GF25	GREY	SERIES HC26, INSERT	2
1	1	1	MALE INSERT	PBT-GF10	GREY	SERIES HC26, INSERT	1
0-3	0-2	0-1					
PN/QTY			DESCRIPTION	MATERIAL	COLOR	NOTE	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±

FINISH

-

DWN H.BRAUN 28OCT2008

CHK T.VETTER 28OCT2008

APVD T.SCHNURPFIL 28OCT2008

PRODUCT SPEC

108-74097

APPLICATION SPEC

114-74103

WEIGHT

-

NAME

MALE INSERT ASS'Y
SERIES HC26, 8-POS., TYPE III+
POWER 4 NET

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=1103428

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE 2:1

SHEET 1 OF 1

REV C2