






SECTION E-E
SCALE 2:1

SECTION F-F
SCALE 2:1

NOTES:


- 1 - RECOMMENDED SEALED AREA
- 2 - THE PRODUCT MUST MEET THE GUIDELINE OF ENVIRONMENTAL CONDITIONS FOR HAZARDOUS SUBSTANCES (GUIDELINE FOR CHEMICAL SUBSTANCES)
- 3 - MARKING FOR CODING: APPLY ASSIGNED COLOR INK
CODING BLACK: NO PRINT
CODING GREY: COLOR GREY
CODING BROWN: COLOR BROWN
- 4 - MATING WITH CMC 28W CONNECTOR
MATERIAL PART NUMBER:
LEFT WIRE OUTPUT CODING BALCK: 64318-1011
LEFT WIRE OUTPUT CODING GREY: 64318-1018
LEFT WIRE OUTPUT CODING BROWN: 64318-1019
RIGHT WIRE OUTPUT CODING BALCK: 64318-3011
RIGHT WIRE OUTPUT CODING GREY: 64318-3018
RIGHT WIRE OUTPUT CODING BROWN: 64318-3019
- 5 - INTERFACE DRAWING REFER TO SD-64318-002.
- 6 - PRODUCT PERFORMANCE: SEE PS-64318-001.



DETAIL H
SCALE 4:1

INSPECTION NUMBER LOG
LAST NUMBER USED: 18
ADDED:
REMOVED:

CMC 28ckt hdr Coding Black	CMC 28ckt hdr Coding Grey	CMC 28ckt hdr Coding Brown	DESCRIPTION
0477450100	0477450200	0477450300	MOLEX MATERIAL NO.
PK-47745-100	PK-47745-100	PK-47745-100	PACKAGING
36.53 g	36.53 g	36.53 g	WEIGHT MEASURED



ITEM	DESCRIPTION	MATERIAL	UNIT	AMOUNT	DIMENSION STYLE			SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
					MM ONLY	INCH	METRIC			
8	Pin 2.8	CuZn30	Piece	5	5	5	DRAWN BY TLUO	DATE 2011/09/23	TITLE CMC 28W R/A HEADER	
7	Pin 1.5	plating 1.3~3.8µm Ni overall	Piece	5	5	5				
6	Pin 0.64(Long)	1~3µm Tin contact side	Piece	13	13	13	CHECKED BY JLOHMAN	DATE 2011/09/23	MATERIAL NO. SD-47745-100	
5	Pin 0.64(Short)	2~4µm Tin Solder side	Piece	5	5	5				
4	Guide Plate	PBT GF30%, UL 94-HB	Piece	1	1	1	APPROVED BY PBERG	DATE 2011/10/26	SHEET NO. 1 OF 1	
3	Housing(Coding: Brown)	Hydrolysis Resistant	Piece	---	---	---				
2	Housing(Coding: Grey)	Color Black	Piece	---	---	---	MOLEX INCORPORATED			
1	Housing(Coding: Black)		Piece	1	---	---	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			