


PART NO. SEE CHART
 DWG. NO. SD-92321-001

90635 CONNECTOR	
CIRCUIT SIZE	
10	
14	
16	
20	
26	
34	
40	
50	



CABLE DETAILS:

28 AWG , 1.27 MM PITCH , 7 STRANDS WITH TINNED COPPER , GREY PVC INSULATION WITH A COLOURED POLARITY STRIPE INDICATING CIRCUIT NO. 1 , UL 2651.

PLATING DETAILS:

15U" GOLD FLASH PLATING.

NOTES:

1. SEE PRODUCT SPECIFICATIONS PS-99020-0015.
2. SEE CABLE SPECIFICATION ES-99027-0006.
3. HARNESSES WILL BE 100% ELECTRICALLY TESTED FOR SHORTS AND DISCONTINUITIES.

ORDERING INFORMATION

92321-****

CIRCUIT SIZE
 LENGTH L IN CENTIMETRES

LENGTHS AVAILABLE FROM 5 CM TO 50 CM, IN STEPS OF 5.
 05, 10, 15, 20, 25, 30, 35, 40, 45 & 50CM

e.g. 92321-1410 = 14 CIRCUIT WITH LENGTH L OF 10 CM.

ORIGINAL RELEASE EC NO. 2000-0896 DRWN: D.RYAN 00/06/15 CHK: / / / / APPR: / / / /	QUALITY SYMBOLS MAJOR = CRITICAL =	GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE 2 : 1	DESIGN UNITS <input checked="" type="checkbox"/> mm <input type="checkbox"/> INCH	THIRD ANGLE PROJECTION <input type="checkbox"/> mm <input type="checkbox"/> INCH <input checked="" type="checkbox"/> mm ONLY	SHT	REV
		4 PLACES ±0. ±.	3 PLACES ±0. ±.	2 PLACES ±0. ±.	1 PLACE ±0. ±.		mm INCH	mm ONLY
REV	DESCRIPTION	ANGULAR: ± 1/2 °		DRAWN BY & DATE D.RYAN 00/03/15		TITLE: QF50 TO QF50 STANDARD ASSEMBLIES		
AI		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		CHECKED BY & DATE BENRIGHT 00/03/15		APPROVED BY & DATE MWILHITE 00/03/15		
		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		CAD FILENAME		MATERIAL NO. SEE CHART		
				DRAWING NO. SD-92321-001		SHEET NO. 1 OF 1		