




CONTACT CAT. N°	FIG.	PACKING	WIRE SIZE		WIRE INSUL. DIAM. IN MM.	WIRE STRIP LENGTH IN MM.	HAND CRIMP TOOLING		EXTRACTION TOOL
			AWG	MM²			DIE SET	HANDTOOL FOR LOOSE PIECE	
SC24W3S25 / SC24W3TK6	1A	3000 PER REEL 100 IN A PLASTIC BAG	26/24	0.12/0.25	0.90/1.60	4.0			RX20D44
SC24WL3S25 / SC24WL3TK6	1B	3000 PER REEL 100 IN A PLASTIC BAG	26/24	0.12/0.25	0.90/1.60	4.0	S20SCM20	SHANGLES	
SC20W3S25 / SC20W3TK6	1A	3000 PER REEL 100 IN A PLASTIC BAG	22/20	0.32/0.50	1.20/2.10	4.0			
SC20WL3S25 / SC20WL3TK6	1C	3000 PER REEL 100 IN A PLASTIC BAG	22/20	0.32/0.50	1.20/2.10	4.0	S20SCM20	SHANGLES	
SM24W3S26 / SM24W3TK6	2A	3000 PER REEL 100 IN A PLASTIC BAG	26/24	0.12/0.25	0.90/1.60	4.0			
SM24WL3S26 / SM24WL3TK6	2B	3000 PER REEL 100 IN A PLASTIC BAG	26/24	0.12/0.25	0.90/1.60	4.0	S20SCM20	SHANGLES	
SM20W3S26 / SM20W3TK6	2A	3000 PER REEL 100 IN A PLASTIC BAG	22/20	0.32/0.50	1.20/2.10	4.0			RX20D44
SM20WL3S26 / SM20WL3TK6	2C	3000 PER REEL 100 IN A PLASTIC BAG	22/20	0.32/0.50	1.20/2.10	4.0	S20SCM20	SHANGLES	

MALE AND FEMALE CONTACTS SIZE 20

CONSTRUCTION

CONTACT BODY : HIGH CONDUCTIVITY COPPER ALLOY.
OUTER SPRING : STAINLESS STEEL.

PACKING CONTACTS ON STRIP : 3000 PCS. PER REEL
PACKING LOOSE PIECE CONTACTS : 100 PCS PER PLASTIC BAG

CONNECTOR ACCOMMODATION

THESE CONTACTS CAN BE USED IN ANY CONTACT POSITION IN ANY CONNECTOR IN THE TRIM TRIO
SEALOK INTERCONNECTION SYSTEM : UTGW CONN., UTOW CONN., UTS CONN.

PERFORMANCE CHARACTERISTICS

CURRENT RATING : 5 A
CONTACT RESISTANCE : <= 15 m Ohm
OPERATING VOLTAGE : 1500 V RMS
CONTACT RETENTION IN BODY : 50 N MIN.
INDIVIDUAL INSERTION FORCE : 5 N MAX.
INDIVIDUAL WITHDRAWAL FORCE : 0.3 N MIN.

PLATING

S25 / S26 = 0.75 µ Au OVER Ni IN CONTACT AREA
GOLD FLASH OVER Ni ON CRIMP BARREL
TK6 = 2-5 µ Sn PREPLATED

CUSTOMER DRAWING

B 18/02/13		UPDATE HAND CRIMP TOOLING ADD DETAIL FOR HEAD P/N S---M.3w		ROUILLARD	LEGER	-
IND. DATE		LIBELLE		REVIS	PAR	CONTROLE PAR (DISTRIBUTION)
DEFINI PAR : A. Janssens		LE: 23-04-97		TYPE DE PLAN: CUSTOMER DRAWING		
VERIFIE PAR: -		LE: -		-		
LES COTES S'ENTENDENT AVANT PROTECTION / FINITION						
DENOMINATION: SEALOK MALE AND FEMALE FORMED CONTACT SM--W(L)3*** / SC--W(L)3***						
ECHELLE	TOLERANCES GENERALES	MATIERE: -	N°: -			
1/1	ANGULAIRES: ± - °	PROTECTION: -	CODE: -			
	LINAIRES: ± -	DEFIANTS DE GEOMETRIE VOIR NF E 04-502	REFERENCE MATERIEL	AFFAIRE TT		
SOURIAU		www.souriau.com		CE DOCUMENT EST LA PROPRETE DE SOURIAU IL NE PEUT ETRE REPRODUIT NI COMMUNIQUE SANS SON AUTORISATION		
FORMAT	REFERENCE PLAN		FOLIO			
A1	BS-C-202338-001		1/1			