


Number of Contact  
(View on Termination Side of Insulator)



NOTES

1. CHARACTERISTICS

Dielectric Withstanding Voltage : 1000 volts rms at sea level.  
 Insulation Resistance : 2000 megohms Min at 500 volts D.C.  
 Contact Resistance : 5 milliohms Max, 1 amps Max

2. RATING

voltage rating : 350 volts rms at sea level  
 Current rating : 5 amps

3. Solder Bucket Size : 1.2 DIA.

4. A DIA. : 10.5 (R.O.)  
 \* ( ) Sleeve at fitting

5. MATERIAL AND TREATMENT

Shell : Zinc Alloy, Nickel plated  
 Coupling Ring : Zinc Alloy, Nickel Plated  
 Insulator : Epoxy Resin  
 Pin Contact : Brass,  
                                     Gold Flash Over Nickel Plated  
 Gasket : Silicon Rubber.  
 Sleeve : Thermotec Plastic Elastomer



記号 SYM	変更 REVISION	品番 ITEM	部品名 DESCRIPTION	材質 MATERIAL	処理 TREATMENT	数量 QTY	備考 REMARKS
		第三角法 PROJECTION	尺度 SCALE 1/1	(TMW) TAJIMI ELECTRONICS CO.,LTD.			
			單位 UNITS mm	製図 DRAWN A. Sugiyama 15 Oct '91	DATE		
		公差 TOLERANCES ON ANGLE .X .XX		設計 ENGR A. Sugiyama 15 Oct '91	DATE	PRC03-12A/10-5M/10.5	
		± ± ±		検図 CHK T. Waki 16 Oct '91	DATE		
		仕様書番号 SPEC NO		承認 APPD S. Nakagawa 16 Oct '91	DATE	PRC03-10-0110	
						SHEET A	