



2		1					
LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			RI	REVISED PER ECO-11-005294	06APR2011	RK	HMR



16.01-16.20
[.630-.638]


6.35-6.47
[.250-.255]

18.16
[.715]



23.62
[.930]


16.13
[.635]




20.57
[.810]

8.26-8.38
[.325-.330]

1. MATES WITH HOUSING 480303 OR 480304.




BLACK	I-480305-9
RED	I-480305-2
NATURAL	I-480305-0
COLOR	PART NUMBER



SCALE 2:1

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 19APR2002	 TE Connectivity				
DIMENSIONS: mm[INCHES]		CHK D. COLEY 19APR2002	NAME CAP, COMMERCIAL MATE-N-LOK™ 3 CIRCUIT				
		APVD D. COLEY 19APR2002					
		PRODUCT SPEC -					
		APPLICATION SPEC -					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-480305	RESTRICTED TO -	
0 PLC ±- 1 PLC ±- 2 PLC ±0.13[.005] 3 PLC ±- 4 PLC ±- ANGLES ±0°30'		CUSTOMER DRAWING					
MATERIAL NYLON, UL94V-2		FINISH -	SCALE 3:1		SHEET 1	OF 1	REV RI