


CAT. NO.	CONFIGURATION	RATING
CS6361C		50A 125V. 2-POLE 3-WIRE
CS8265C		50A 250V. 2-POLE 3-WIRE
CS8465C		50A 480V. 2-POLE 3-WIRE
CS6365C		50A 125/250V 3-POLE 4-WIRE
CS8365C		50A 250V. 3-PHASE 3-POLE 4-WIRE
CS8165C		50A 480V. 3-PHASE 3-POLE 4-WIRE
HBL3763C		50A 250V. 50A 600V. 2-POLE 3-WIRE
HBL3765C		50A 250VDC 50A 600 VAC 3-POLE 4-WIRE
HBL7765C		50A 250VDC 50A 600 VAC 3-POLE 4-WIRE

M-6590 6

USE ROUND CORD TYPES:
S, SO, ST, 8/3 - 4/4
Ø .83 [21.08] TO Ø 1.25 [31.75]



DEVICE MAY BE SHIPPED
WITH REAR HOUSING AND CORD
GRIPS UNASSEMBLED

NOTE: ALL DIMS. ARE IN INCHES
[mm]

LIST OF PARTS			
DESCRIPTION	MATERIAL	FINISH	
FRONT HOUSING	NYLON		
BLADE HOLDER	POLYESTER		
POWER BLADES	BRASS		
GRD. CONT. SPR.	COPPER NICKEL		
GRD. CONTACT RIVET	BRASS		
SHELL	STAIN. ST.		
RETAINER	POLYESTER		
BOX TERMINAL	COPPER		
TERM. SET SCR.	STAIN. ST.		
SEAL	NEOPRENE		
SEAL CUP	NYLON		
REAR HOUSING	NYLON		
CORD GRIPS	POLYESTER		
GRIP SCREWS	STAIN. ST.		
LATCHES	NYLON		

6	REVISED CORD GRIP RANGE CALL OUT PER DCN 16806 RCM	TLS	6/8/10
5	ADDED [mm] EQUIV TO DIMS.; ADDED NOTE FOR [mm]; CS8465C WAS CS6365C PER DCN 13418 RCM	JPP	10/10/06
4	CONVERTED ALL DIMS TO 3 PL DECIMAL. REMOVED DASHES FROM CS & ADDED HBL PREFIXES TO CAT # PER DCN 7772. AMZ	DB	7-5-00
3	2 3/8 DIA. WAS 2 1/2 DIA. AUL	MP	12-4-89
2	GR. CONT. SPR. WAS BRASS CORD GRIPS WERE NYLON REMOVED CAT NO. 63CHG163 CHG 65C		11-22-89
1	FOR 250V 3P 4W 125/250V 50A 250V 3P 4W 125/250V		8-4-89
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE.			
--	--	--	--

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE DIVISION HARVEY HUBBELL, INC. BRIDGEPORT, CONN.	
FRACTIONS ± 1/64	DR. BY A.J.L.	APP. BY
DECIMALS ± .005	TR. BY	SCALE 1:1
ANGLES ± 2°	CHK'D. BY	DATE 7-9-87

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-6590 6

CODE 74545

TITLE

50A TWIST-LOCK PLUGS
THREE AND FOUR WIRE