



CAT. NO.	CONFIGURATION	RATING
CS6360C		50A 125V. 2-POLE 3-WIRE
CS8264C		50A 250V. 2-POLE 3-WIRE
CS8464C		50A 480V. 2-POLE 3-WIRE
CS6364C		50A 125/250V 3-POLE 4-WIRE
CS8364C		50A 250V. 3-PHASE 3-POLE 4-WIRE
CS8164C		50A 480V. 3-PHASE 3-POLE 4-WIRE
HBL3762C		50A 250VDC 50A 600 VAC 2-POLE 3-WIRE
HBL3764C		50A 250VDC 50A 600 VAC 3-POLE 4-WIRE
HBL7764C		50A 250 VDC 50A 600 VAC 3-POLE 4-WIRE

M-6591 5

USE ROUND CORD TYPES:
S, SO, ST, 8/3 - 4/4
Ø .83 [21.08] TO Ø 1.25 [31.75]



DEVICE MAY BE SHIPPED WITH REAR
HOUSING & CORD GRIPS
UNASSEMBLED.

TITLE
50A TWIST-LOCK CONNECTORS
THREE AND FOUR WIRE

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
CONTACT NOSE	NYLON	
PIN - CS	STAIN. ST.	
HOLDER CONTACT	POLYESTER	
CONTACT SPRING	BRASS	
RIVET	BRASS	
BOX TERMINAL	COPPER	
TERMINAL SET SCR.	STAIN. ST.	
GRD. CONTACT	COPPER	
RETAINER	POLYESTER	
ASS'Y. RING	STAIN. ST.	
FRONT HOUSING	NYLON	
SEAL	NEOPRENE	
SEAL CUP	NYLON	
REAR HOUSING	NYLON	
CORD GRIPS	POLYESTER	
GRIP SCREWS	STAIN. ST.	
LATCHES	NYLON	

5	REVISED CORD GRIP RANGE CALLOUT PER DCN 16606	TLS	8/8/10
4	CONVERTED ALL DIMS TO 3 PL DECIMAL, REMOVED DASHES FROM CS & ADDED HBL PREFIXES TO CAT # PER DCN 7772. AMZ DB		7-5-00
3	CORDED MATL WAS NYLON 6 1/2" LENGTH, 1/8" DIA. 6 1/2" DIA. 6 1/2" DIA. 1/8" DIA. 6 1/2" DIA.	MM	12-4-89
2	REMOVED GRD. TERMINAL REMOVED GRD. TERMINAL REMOVED GRD. TERMINAL		11-22-89
1	REMOVED GRD. TERMINAL REMOVED GRD. TERMINAL REMOVED GRD. TERMINAL		8-4-89
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE.

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE DIVISION HARVEY HUBBELL, INC. BRIDGEPORT, CONN.	
FRACTIONS ± 1/64	DR. BY AJL	APP. BY
DECIMALS ± .005	TR. BY	SCALE 1:1
ANGLES ± 2°	CHK'D BY	DATE 7-9-87

CODE 74545

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-6591

5