



**1.0 ELECTRICAL**

- 1.1 FREQUENCY RANGE: DC-250 MHz
- 1.2 NOMINAL IMPEDANCE: 75 OHMS

**2.0 MATERIALS**

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604

**3.0 FINISHES AND OTHERS**

- 3.1 SEE BELOW TABLE FOR DETAILS.

**4.0 ENVIRONMENTAL**

- 4.1 OPERATING TEMPERATURE RANGE: -20° C TO +60° C

9	CENTER CONTACT	BRASS	1	NICKEL
8	INSULATION	POM	1	NONE
7	BODY	BRASS	1	NICKEL 100μ" MIN.
6	WASHER	BRASS	1	NICKEL
5	SPRING WASHER	SK-5	1	NICKEL
4	WASHER	BRASS	1	NICKEL
3	GASKET	RUBBER	1	RED
2	INSULATION	POM	1	NONE
1	SHELL	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED by \_\_\_\_\_ DATE: \_\_\_\_\_

DESCRIPTION		STRAIGHT BNC PLUG - RCA JACK ADAPTER							
製圖	DRAWN	TOLERANCE	品名	13-46-2	D.N.N	日期	DATE	版次	REV.
	<i>Kristina</i>								
檢圖	CHECK	單位	單	UNIT	DWG.NO.	13-0678	佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.		
	<i>Ivan</i>								
認定	APPROVAL	.XXX ±0.05	比例	SCALE					
<i>Angela</i>	ANGLE	±5°	4:1						