


NO	DESCRIPTION	DATE
△	MODIFY PARTS ①④ 25.0 → 22.0 33.6±0.5 → 30.5±0.5	08.05.13'



**1.0 ELECTRICAL**

- 1.1 FREQUENCY RANGE: DC-250 MHz
- 1.2 NOMINAL IMPEDANCE: 75 OHMS

**2.0 MATERIALS**

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604

**3.0 FINISHES AND OTHERS**

- 3.1 SEE BELOW TABLE FOR DETAILS.

**4.0 ENVIRONMENTAL**

- 4.1 OPERATING TEMPERATURE RANGE: -40° C TO +60° C

5	INSULATION	POM	1	NONE
4	CENTER CONTACT	BRASS	1	GOLD
3	INSULATION	POM	1	NONE
2	WASHER	BRASS	1	NICKEL
1	BODY	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED by \_\_\_\_\_ DATE: \_\_\_\_\_

DESCRIPTION		STRAIGHT RCA PLUG - BNC JACK ADAPTER						
製圖	DRAWN	TOLERANCE	品名	14-05-1 D.G.N	日期	DATE	版次	REV.
	Yoko							
檢圖	CHECK	單位	單位	DWG.NO.	14-0013	佳楠精密電子股份有限公司 CHIN NAN PRECISION ELECTRONICS CO.,LTD.		
	Angela							
認定	APPROVAL	XXX ±0.05	比例	SCALE	4:1			
	Angela	ANGLE ±5°						