


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	MIN. CABLE LENGTH
NK5EPC3**Y	3 FT.
NK5EPC5**Y	5 FT.
NK5EPC7**Y	7 FT.
NK5EPC10**Y	10 FT.
NK5EPC14**Y	14 FT.
NK5EPC20**Y	20 FT.
NK5EPC1M**Y	1 METER
NK5EPC2M**Y	2 METERS
NK5EPC3M**Y	3 METERS
NK5EPC5M**Y	5 METERS

- NOTES:
IDENTIFICATION:
- SEE CURRENT NETKEY CATALOG FOR PACKAGE QUANTITIES AND AVAILABLE COLORS.
 - SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
 - TERMINATED WITH (8-POSITION) MODULAR PLUGS ON BOTH ENDS PER T568A.
 - CONSTRUCTED WITH 4-PAIR/24 AWG STRANDED UTP CAT 5e NON-PLENUM PATCH CABLE.
 - MATERIAL:
PLUG: POLYCARBONATE

D T568A WIRING SCHEME

PLUG POSITION	CABLE WIRE
1	WHITE GREEN
2	GREEN
3	WHITE ORANGE
4	BLUE
5	WHITE BLUE
6	ORANGE
7	WHITE BROWN
8	BROWN

MODEL FILENAME	D35123CT_CAT5100_07	SIZE	A
DRAWING FILENAME	M02479LL_DC299_00B.PRT		
TITLE	NETKEY CATEGORY 5e PATCH CORD CUSTOMER DRAWING		
	PANDUIT TM CORP. TINLEY PARK, ILL 60477	I.I. NUMBER	
	THIRD ANGLE PROJECTION	PRODUCT SPEC	
	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.	WORK INSTRUCTION	
	DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ± 1°	SCALE	NONE
DRAWN BY	NER	REVIEW DRAWING NUMBERS	PART NO. NK5EPC**Y
DATE	3-21-06		DRAWING NO. 02479-299
CHK'D	WJC		

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
1	5-29-07	BJN	EJH	D. ADDED T568A WIRING SCHEME C. MODULAR WAS PANDUIT B. ADDED NOTES 3-5 A. ADDED METRIC LENGTHS	02479-299		REGA		
R	3-21-06	NER	WJC	RELEASED TO PRODUCTION	02479-299		RMD		