





D

C

B

A



SECTION Y-Y

- 1 SEE TABLE FOR RIB QTY
- 2 THIS COUPLING SHROUD IS TO BE USED WITH AMPMODU<sup>®</sup> MTE RECEPTACLE ASSEMBLIES WITH GUIDE RIBS. THE NUMBER OF POSITIONS LISTED EQUALS THE TOTAL NUMBER OF POSITIONS WHICH CAN BE CONTAINED WITHIN THE COUPLING SHROUD.
- 3 .133 BETWEEN RIBS REFERENCED BY NOTE 1 ONLY. .153 ON ENDS ( AREAS OUTSIDE OF THE RIBS ).
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

|            |       |       |       |            |             |
|------------|-------|-------|-------|------------|-------------|
|            |       |       |       |            |             |
|            |       |       |       |            |             |
|            |       |       |       |            |             |
|            |       |       |       |            |             |
|            | 2.460 | 2.505 | 2.685 | 2          | 50          |
|            | 1.960 | 2.005 | 2.085 | 2          | 40          |
| 4 OBSOLETE | 1.660 | 1.705 | 1.885 | 2          | 34          |
|            | 1.560 | 1.605 | 1.785 | 2          | 32          |
|            | 1.460 | 1.505 | 1.685 | 2          | 30          |
| OBSOLETE   | 1.360 | 1.405 | 1.585 | 2          | 28          |
|            | 1.260 | 1.305 | 1.485 | 2          | 26          |
|            | 1.160 | 1.205 | 1.385 | 2          | 24          |
|            | 1.060 | 1.105 | 1.285 | 2          | 22          |
|            | .960  | 1.005 | 1.185 | 2          | 20          |
| 4 OBSOLETE | .860  | .905  | 1.085 | 2          | 18          |
|            | C     | B     | A     | NO OF RIBS | NO OF POSN  |
|            |       |       |       |            | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN  
D KEITZER  
CHK  
S SHUEY  
APVD  
C SINISI

01DEC88  
07DEC88  
14DEC88

TE Connectivity

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± .010  
4 PLC ± - ± -  
ANGLES

PRODUCT SPEC  
108-25034  
APPLICATION SPEC  
114-25026

MATERIAL  
FLAME RETARDANT THERMOPLASTIC  
COLOR-BLACK

FINISH -

WEIGHT -

SIZE  
A1

CAGE CODE  
00779

DRAWING NO  
104500

RESTRICTED TO -

CUSTOMER DRAWING

SCALE  
4:1

SHEET  
1

OF  
1

REV  
L2