


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NUMBER	MARKER SIZE	MATERIAL
LS7-25-1	.236 X 26.2 (6.00 X 8.0)	BLK/WHT LAM. POLYESTER
LS7-25-2	.236 X 26.2 (6.00 X 8.0)	BLK/CLEAR LAM. POLYESTER
LS7-38-1	.354 X 26.2 (9.00 X 8.0)	BLK/WHT LAM. POLYESTER
LS7-38-2	.354 X 26.2 (9.00 X 8.0)	BLK/CLEAR LAM. POLYESTER
LS7-50-1	.472 X 26.2 (12.00 X 8.0)	BLK/WHT LAM. POLYESTER
LS7-50-2	.472 X 26.2 (12.00 X 8.0)	BLK/CLEAR LAM. POLYESTER
LS7-75-4	.708 X 26.2 (18.00 X 8.0)	BLK/YEL LAM. POLYESTER
LS7-75-5	.708 X 26.2 (18.00 X 8.0)	BLK/ORN LAM. POLYESTER
LS7-75-6	.708 X 26.2 (18.00 X 8.0)	BLK/RED LAM. POLYESTER
LS7-75NL-1	.708 X 26.2 (18.00 X 8.0)	BLK/WHT NON-LAM. POLYESTER
LS7-75NL-2	.708 X 26.2 (18.00 X 8.0)	BLK/CLEAR NON-LAM. POLYESTER
LS7-ACS	.236 X 26.2 (6.00 X 8.0)	BLK/WHT LAM. POLYESTER
LS7-CLN	.236 X 26.2 (6.00 X 8.0)	BLK/WHT LAM. POLYESTER
UILS7BW	.236 X 26.2 (6.00 X 8.0)	BLK/WHT NON-LAM. POLYESTER

NOTES:
1. DIMENSIONS IN []
ARE IN MILLIMETERS.

											PANDUIT	CORP	TINLEY PARK, ILLINOIS
											CUSTOMER DRAWING LS7 CASSTTE		
											UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XX) ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
											UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.XXX) ± ANGLES ±		
										DRAWN BY RVU	MAT'L:		SCALE FULL
O	6-20-06	RVU		ENGINEERING RELEASE.	4561	R				DATE 6-20-06	CASSETTE - THERMOPLASTIC		DRAWING NO. C10425
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	CHK'D			DWG B SIZE