+


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART# DESCRIPTION WEIGHT

NK6TM\*\*

B POSITION, 8 WIRE UNIVERSAL MODULE, 1.43 LB/100 PCS TERMINATION CAP IS COLOR CODED FOR 1649g/100 PCS)


(649g/100 PCS)





PANEL OPENING REQUIREMENTS
PANEL THICKNESS: .048"-.058"
(1.22mm-1.47mm)

## NOTES:

- 1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND PACKAGE QUANTITY.
- 2. MATERIAL:
  MODULE HOUSING- ABS
  NOMINAL WALL THICKNESS .078(2.0).
  PRESERVATION CAP-PC
- 3. ALL NETKEY CAT6, 8 POSITION, 8 WIRE JACK MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION PAIR MODULAR PLUGS WITHOUT DAMAGE.
- 4. THIS PART IS DESIGNED FOR USE WITH STANDARD KEYSTONE OPENINGS.
- 5. DIMENSIONS IN PARENTHESES ARE IN METRIC.







ACTUAL SIZE

										MO1336AI_TX6P_KSTN_ASSBY_OO.PRT SIZE MO1336EJ_DC41_OOA.PRT		
										TITLE NET	KEY CATEGORY 6 CUSTOMER DRA	
										T	TM CORP.	I.I. NUMBER PRODUCT SPEC WORK INSTRUCTION
										THIRD ANGLE PROJECTION DRAWN BY	(.XX) ±.03(.8) ANGLES ±	SCALE NONE
R	5-12-03	MDJr		RELEASED TO PRODUCTION	01336-41					MDJr <b>DATE</b> 5-6-03		NK6TM**
REV	DATE	BY	снк	DESCRIPTION	ECN -	R	CUST	SUP	отн	CHK.D		01336-41

+

4