



LOC	DIST	REVISIONS					
J	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER ECR-10-013244	10JUL2010	HMR	TM
			C	REVISED	27JUN2011	M.M	N.Y




1. MATERIAL: HOUSING: GLASS FILED THERMO PLASTIC
POLYESTER (94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
SPRING: STAINLESS STEEL

△2.FINISH(ALL OVER):NICKEL PL. 1.27μmMIN

△3.FINISH(CONTACT AREA):GOLD PL. 0.3μmMIN AFTER △2.



38	18	63.0	70.1	67.0	77.7	REC ASSY:2-1871940-9
30	14	49.0	56.1	53.0	63.7	REC ASSY:2-1871940-5
22	10	35.0	42.1	39.0	49.7	REC ASSY:2-1871940-1
16	7	24.5	31.6	28.5	39.2	REC ASSY:1-1871940-8
12	5	17.5	24.6	21.5	32.2	REC ASSY:1-1871940-6
8	3	10.5	17.6	14.5	25.2	REC ASSY:1-1871940-4
POS.	n	A	B	C	D	PART No.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. TAKADA 09APR2007 CHK J. AKASAKA 09APR2007 APVD J. AKASAKA 09APR2007		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: $\pm 0.3, \pm 3^\circ$		NAME DYNAMIC D1900D 3.5mm PITCH REC ASSY (SPRING CLAMP TYPE) 8-38POS	
		0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm$			
MATERIAL 		FINISH 		PRODUCT SPEC 108-78336	
		APPLICATION SPEC -		SIZE A3	
		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-1871940	
				RESTRICTED TO -	
				SCALE 4:1	
				SHEET 1 OF 1	
				REV C	