


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	ECN	DATE	APVD
J	-						
		A1		PART NO ADDITION		22MAR2007	M.M D.M
		A2		DRAFTING ERROR	ECR-07-005648	23OCT2007	M.M S.M
		B		REVISED	ECR-07-025215	07NOV2008	M.M A.O
		C		REVISED		25NOV2009	Y.O T.K



1. MATERIAL: GLASS FILED THERMO PLASTIC POLYESTER(94V-0), COLOR: BLACK
2. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.
3. THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".
1. 材料: ガラス入り熱可塑性ポリエステル樹脂(94V-0), 色: 黒
2. 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません。
3. Y KEY形状はX KEY形状と左右対称

40	Y	19	38.0	40.9	42.6	2-1827863-0
40	X	19	38.0	40.9	42.6	1-1827863-0
34	Y	16	32.0	34.9	36.6	2-1827863-7
34	X	16	32.0	34.9	36.6	1-1827863-7
32	X	15	30.0	32.9	34.6	1-1827863-6
30	X	14	28.0	30.9	32.6	1-1827863-5
28	X	13	26.0	28.9	30.6	1-1827863-4
26	Y	12	24.0	26.9	28.6	2-1827863-3
26	X	12	24.0	26.9	28.6	1-1827863-3
24	X	11	22.0	24.9	26.6	1-1827863-2
22	X	10	20.0	22.9	24.6	1-1827863-1
POS	KEY	n	A	B	C	PART NO

40POS(X-KEY): 1-1827863-0

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
単位: 概
mm

MATERIAL
材料

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差 ±0.3, ±5°
0-PLC ±
1-PLC ±0.1
2-PLC ±0.02
3-PLC ±0.005
4-PLC ±0.0005
ANGLES ±
FINISH
仕上

DWN
T. KUDO
CHK
D. MITSUGI
APVD
D. MITSUGI
PRODUCT SPEC
製品規格
108-78268, 78298
APPLICATION SPEC
取付適用規格
114-5377
WEIGHT
-
CUSTOMER DRAWING

16MAR2005
23AUG2005
23AUG2005

Tyco Electronics Corporation
Kawasaki, Japan

NAME
名称
DYNAMIC D1100D 2.0mmPITCH
REC HSG
22-40POS

SIZE
A3
CAGE CODE
00779
DRAWING NO
C=1827863
RESTRICTED TO
-

SCALE
尺度
2:1
SHEET
1
OF
3
REV
C

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR
















DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1 OF 3



22POS(X-KEY): 1-1827863-1

26POS(X-KEY): 1-1827863-3

28POS(X-KEY): 1-1827863-4

30POS(X-KEY): 1-1827863-5

32POS(X-KEY): 1-1827863-6

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±

MATERIAL

FINISH

DWN T. KUDO 16MAR2005

CHK D. MITSUGI 23AUG2005

APVD D. MITSUGI 23AUG2005

PRODUCT SPEC

108-78268, 78298

APPLICATION SPEC

114-5377

WEIGHT

CUSTOMER DRAWING

Tyco Electronics Corporation
Kawasaki, Japan

NAME

DYNAMIC D1100D 2.0mmPITCH
REC HSG
22-40POS

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-1827863

SCALE 2:1

SHEET 2 OF 3

REV C

