


NUMBER 177662







METRIC

PROJ NO.392-610

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST

AMP-J
REV.10/83



NOTES

1. MATERIAL:HOUSING:GLASS FILED THERMO
PLASTIC,UL94V-0
CONTACT:COPPER ALLOY
RETENTION LEG:COPPER ALLOY

- △2. FINISH(CONTACT AREA):0.38μmMIN GOLD PLATING
OVER Ni PLATING
- △3. FINISH(CONTACT AREA):0.76μmMIN GOLD PLATING
OVER Ni PLATING
- △4. FINISH(RETENTION LEG): TIN PLATED
(SOLDER TYING) OVER NICKEL

注記

- 1. 材料:ハウジング: ガラス入り熱可塑性
樹脂,UL94V-0
コンタクト: 銅合金
リテンションレグ: 銅合金
- △2. めっき: コンタクト接触部: ニッケル下地の上に
金めっき0.38μmMIN
- △3. めっき: コンタクト接触部: ニッケル下地の上に
金めっき0.76μmMIN
- △4. めっき: リテンションレグとコンタクト半田付部
: ニッケル下地の上にスズめっき

△4	△3	1-177662-3
△4	△2	1-177662-2
(FINISH)		製品番号 (PART NO.)

A	REVISED(FJD0-0039-03)	TS	SM	6/2/93	
0	RELEASED (FJ00-0284-93)	NM	SM	9/30/93	
LTR	REVISION RECORD	DR	CHK	DATE	

Copyright © 1993 AMP(Japan) LTD. ALL RIGHTS RESERVED.				Tyco Electronics AMP K.K. Kawasaki, Japan	
WIRE RANGE mm²(AWG -)		INSULATION DIA mmφ		NAME 5 POS SINGLE ROW SMT TYPE HORIZONTAL HDR ASS'Y FOR DYNAMIC 3100	
MATERIAL SEE NOTE 注記参照		FINISH SEE NOTE 注記参照		一般公差 (GENERAL TOLERANCE)	
DR. 20 SEP 93 N. Matsubara		DE. 20 SEP 93 N. Matsubara		SIZE A3	LOC J
CHK. 30 SEP 93 S. MANABE		APP. 30 SEP 93 S. MANABE		SCALE 2-1	REV. A
				NUMBER C-177662	SHEET 1 OF 1

(CUSTOMER DRAWING) 顧客用図面