




LOC	DIST	REVISIONS				
J	—	P	LTR	DESCRIPTION	DATE	APVD
		E		REVISED	27JUN2012	H.M N.Y

NOTES


1 MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
POLYESTER(94V-0),
COLOR:1- /2- : BLACK
: 9- : NATURAL





2 TO COAT ALL SURFACE OF HOUSING WITH TEFLON



2.5XN=A

KEY LOCATION VIEW
2-1318119-4
(KEYING Y)




 KEYING:Y 2-1318119-4 9-1318119-4	 KEYING:Y 2-1318119-3 9-1318119-3
 KEYING:X 1-1318119-4	 KEYING:X 1-1318119-3

OBSOLETE		11.4	10.8	7.5	3	8	5-1318119-4
	—	11.4	10.8	7.5	3	8	9-1318119-4 2-1318119-4
	—	11.4	10.8	7.5	3	8	1-1318119-4
OBSOLETE		8.9	8.3	5	2	6	5-1318119-3
	—	8.9	8.3	5	2	6	9-1318119-3 2-1318119-3
	—	8.9	8.3	5	2	6	1-1318119-3
FINISH		C	B	A	N	POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

± 0.3
± 0.35
± 0.4
± 3°

10
30
100

>10
>30
>100

DWN
K.IKEDA
CHK
N.MATSUBARA
APVD
I.HASEGAWA
PRODUCT SPEC
108-5619
APPLICATION SPEC
114-5258
WEIGHT
T1

07DEC1998
07DEC1998
07DEC1998

 TE Connectivity

DOUBLE ROW REC HSG
DYNAMIC D-2100D
—

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1318119

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
1 OF 1

REV
E

1470-19 (3/11)