






353715



ΣΕΤΡΙC

单位: 耗 DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DIST



注記

- | | |
|---|----------------------|
|  | 標準接圧型コンタクト：一般向け及び多極用 |
|  | 高接圧型コンタクト：高電流用及び強振動用 |
|  | 金めっきは接触部のみとする |

NOTES

- | | | | |
|---|---|--|--|
| ① | CONTACT TYPE;LOW PRESSURE TYPE(FOR GENERAL) | | |
| ② | CONTACT TYPE;HIGH PRESSURE TYPE
(FOR HIGH CURRENT OR ANTI-VIBRATION) | | |
| ③ | GOLD-PL. CONTACT AREA ONLY | | |

		5	光沢錫めっき(BRIGHT TIN-PL.)	1- ↑ -5	1- ↑ -5
	H	3	0.76μm最小金めっき(0.76μmMIN.Au-PL.)	1- -3	1- -3
		2	0.38μm最小金めっき(0.38μmMIN.Au-PL.)	1- -2	1- -2
A	/	3	0.76μm最小金めっき(0.76μmMIN.Au-PL.)	-3	-3
		2	0.38μm最小金めっき(0.38μmMIN.Au-PL.)	353717-2	353715-2
備考(REMARK) 接点タイプ	接圧表示 (ID-MARK) (CONT. TYPE)	めっきコード (PL. ID NO)	仕上(FINISH)	△ 単体(L/P)	型番(P/N)

						③ COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		 Tyco Electronics Kawasaki, Japan	
						組合電線断面図 (WIRE RANGE) AWG 16-14		被覆外径 (INSULATION DIA.) 3.1-3.4 mmφ	
						名称 (NAME) "3L" SIZE (DYNAMIC SERIES REC. CONTACT) ダイナミックシリーズリセプタクルコンタクト			
B	REVISED	Y.O.T.K.	07DEC 2009	材料 (MATERIAL) (COPPER ALLOY) 銅合金		仕上 (FINISH) (SEE TABLE) 表参照		一般公差 (GENERAL TOLERANCE)	
A	REVISED (FJ00-0690-97)	K.I.N.M.	8/MAY '97	DR. 7/FEB/'97 K.IKEDA		DE. 7/FEB/'97 K.IKEDA		10mm : ±0.2 10mm 以下 : ±0.25 30mm 以下 : ±0.3 角 度 : ±3°	SIZE A3
O	RELEASED (FJ00-5891-97)	K.I.Y.	12/FEB '97	CHK. 12/FEB/'97 Y.ISHIKAWA		APP. 12/FEB/'97 Y.ISHIKAWA		10mm 以下 : ±0.25 30mm 以下 : ±0.3 角 度 : ±3°	LOC J
LTR 変更 (REVISION RECORD)		DR	CHK	DATE					番号 (No.) 353715
									尺度 (SCALE) 5-1
									REV. B
									SHEET 1 OF 1