




Loading-Plan:

- | | |
|---|-------|
| 1 | brown |
| 2 | white |
| 3 | blue |
| 4 | black |

For Information Only
won't be replaced when changed



Recommended panel cut-out



Minimum wall thickness 1.5mm

- Protection level: IP67
- Temperature range: -30°C ... +80°C

1	21023576405	AWG 24, PVC	0.5
Cont. No.	Part - no.	Type of cable	Dim. a[m]

	All rights reserved		Scale 2:1	Free size tol.		Ref.	
	Department EC PD - RO		Created by TAMAS	Inspected by	Standardisation	Date 2014-06-18	State Checked Out
HARTING Electronics GmbH		Title M8 Cable Assembly				Doc-Key / ECM-Nr. 100580445/UGD/009/A	
D-32339 Espelkamp		Type TB	Number 210235764XX			Rev. A	Page 1/1