






Loading-Plan:


- | | |
|---|-------|
| 1 | brown |
| 3 | blue |
| 4 | black |

For Information Only
won't be replaced when changed

Recommended panel cut-out



Minimum wall thickness 1.5mm



- Protection level: IP67
- Temperature range: -30°C ... +80°C

1	21033176305	AWG 24, PVC	0.5
Cont. No.	Part - no.	Type of cable	Dim. a[m]

		All Dimensions in mm Original Size DIN A3		Scale 2:1		Free size tol.		Ref.							
		All rights reserved		Created by TAMAS		Inspected by		Standardisation		Date 2014-06-19		State Checked Out			
		Department EC PD - RO		Title M12 A-coded Cable Assembly								Doc-Key / ECM-Nr. 100580453/UGD/009/A			
HARTING Electronics GmbH D-32339 Espelkamp				Type TB		Number 210331763XX						Rev. A		Page 1/1	