






Loading-Plan:


- | | |
|---|-------|
| 1 | brown |
| 2 | white |
| 3 | blue |
| 4 | black |

For Information Only
-won't be replaced when changed-

Recommended panel cut-out



Minimum wall thickness 1.5mm



- Protection level: IP67
- Temperature range: -30°C ... +80°C

1	21033176405	AWG 24, PVC	0.5
Cont. No.	Part - no.	Type of cable	Dim. a[m]

		All Dimensions in mm Original Size DIN A3		Scale 2:1		Free size tol.		Ref.							
								Sub.							
		All rights reserved		Created by TAMAS		Inspected by		Standardisation		Date 2014-06-19		State Checked Out			
		Department EC PD - RO		Title M12 A-coded Cable Assembly								Doc-Key / ECM-Nr. 100580483/UGD/009/A			
HARTING Electronics GmbH				Type TB		Number 210331764XX						Rev. A		Pag. 1/	
D-32339 Espelkamp															