







Loading-Plan:

- | | | |
|---|---|-------|
| 1 | — | brown |
| 2 | — | green |
| 3 | — | blue |
| 4 | — | red |

For Information Only
-won't be replaced when changed-



Recommended panel cut-out



Minimum wall thickness 1.5mm

- Protection level: IP67
- Temperature range: -30°C ... +80°C

1	21033386405	AWG 24, PVC	0.5
Cont. No.	Part - no.	Type of cable	Dim. a[m]

	All Dimensions in mm Original Size DIN A3		Scale 2:1	Free size tol.		Ref.
	All rights reserved Department EC PD - RO		Created by TAMAS	Inspected by	Standardisation	Sub.
HARTING Electronics GmbH D-32339 Espelkamp		Title M12 B-coded Cable Assembly				Doc-Key / ECM-Nr. 100581424/UGD/009/A
		Type TB	Number 210333864XX			Rev. A
					Page 1/1	