




AMP WIRE RANGE	E13288 Listed
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED

LR7189 Certified	MILITARY P/N AND CLASS
16-14 AWG SOLID OR STRANDED	M7928/7-10 CLASS 2 P/N 34126 & 2-34126-2 ONLY

- 1

STAMP AMP 16-14* APPROX AS SHOWN
- 2

TIN PLATE 0.00254 [.000100] MIN THK
PER ASTM B-545.
- 3

GOLD PLATE 0.00127 [.000050] MIN THK
PER MIL-G-45204 OVER NICKEL PLATE
0.00076 [.000030] MIN THK PER
QQ-N-290.
- 4

PRELIMINARY - NOT FOR PRODUCTION

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm ² [2,050-5,180] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

3 2 2 2	---- 100 5000 ---	LOOSE PIECE LOOSE PIECE, BOX ON TAPE LOOSE PIECE	4 2-34126-1 8-34126-1 2-34126-2 34126
FINISH	QUANTITY	PACKAGING TYPE	PART NO
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-17-93 CHK DA PATTERSON 3-17-93 APVD DE MILLER 3-17-93 PRODUCT SPEC APPLICATION SPEC WEIGHT -	TE Connectivity NAME TERMINAL, RING TONGUE, SOLISTRAND™
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	SIZE A2	CAGE CODE 00779
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH SEE TABLE	DRAWING NO C=34126	RESTRICTED TO -
MATERIAL COPPER PER ASTM B-152 ANNEALED	SCALE 8:1	SHEET 1 of 1	REV H1
CUSTOMER DRAWING			