



LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	DWN
		G		REV PER ECR 09-004073	20FEB09	JR
						APVD
						TM


AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
24-20 AWG SOLID OR STRANDED	22-20 AWG SOLID OR STRANDED	22-20 AWG SOLID OR STRANDED



- 1 STAMP AMP APPROX AS SHOWN
- 2 MAXIMUM LENGTH DOES NOT INCLUDE MANUFACTURING TABS
- 3 COPPER PER ASTM B-152, ANNEALED
- 4 TIN PLATE 0.00254 [.000100] MIN PER ASTM B-545
- 5 CLEANED, UNPLATED



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 0.16-0.65mm² [320-1,290] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-13-93		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
DIMENSIONS: MM[INCHES]		CHK DA PATTERSON 4-13-93					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD JL MECKLEY 4-13-93		NAME SPLICE, BUTT, STRAP, SOLISTRAND		
			PRODUCT SPEC —				
			APPLICATION SPEC —				
MATERIAL COPPER 	FINISH SEE TABLE	WEIGHT —		SIZE A2	CAGE CODE 00779	DRAWING NO C=324001	RESTRICTED TO —
		CUSTOMER DRAWING				SCALE 10:1	SHEET 1 of 1