




DESCRIPTION: IP67 - 9 POSITION PLASTIC BACKSHELL - ONLY



**TORQUE
SETTING**
6.075-9.547 in.lbs
[7-11 kgf.cm]

MATERIAL & FINISH:

- BACKSHELL: ABS - UL HB RATED, BLACK COLOR
- BUSHING & BAFFLE: SILICONE
- THUMBSCREWS: BRASS, NICKEL PLATED
- TEMPERATURE: -50°C TO 125°C
- CABLE DIAMETER: 0.260 inches [6.60mm] Max.
0.100 inches [2.54mm] Min.



DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: M. SIGMON DATE: 12-2-10

CHECKED: DATE:

SCALE: 2 : 1 SHEET 1 OF 1 REV 4

DWG NO. 967-009-010R011

NorComp

RoHS COMPLIANT